



### **Product description**

Order number	78.898
Product description	Mailing container 126 x 30 mm, with absorbent liner, without cap

### **Product characteristics**

Application	Mailing of samples
Example of use	Secondary packaging according to P 650
Absorbent liner	yes
Shape of opening	round
Liquid-tight	yes

### **Size**

Diameter of opening	30 mm
Length of product	126 mm

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

This specification is confidential and the property of Sarstedt. It is neither to be duplicated nor made available to third parties without our prior written consent.





### **Material & colours**

Product material	Polypropylene (PP)
Colour of product	transparent

### **Purity & certification**

Satisfies the requirement	P 650, ADR
Pyrogen-free	no

### **Packaging**

Minimum order qty.	250
Pcs. / inner box	50
Pcs. / box	250
Pcs. / pallet	7500
Depth of case	398 mm
Width of case	358 mm
Height of case	325 mm
Case volume	0,0463 cbm
Weight of case	4,23 kg
EAN of inner box	4038917084543
EAN of outer box	4038917003353

This is the current specification for this product. Sarstedt reserves the right to make changes, in full or in part, at any time without prior notification.

This specification is confidential and the property of Sarstedt. It is neither to be duplicated nor made available to third parties without our prior written consent.

