

Qufora® IrriSedo Cone

For high volume transanal irrigation

Description

Qufora IrriSedo Cone includes:

- A.** 1500 ml waterbag, connected to a tube with a valve and a pump
- B.** Single-use cone with hydrophilic coating that is activated when dipped in water

Accessories

Single-use cones

Features

- The soft single-use cone is coated so when dipped in water it is ready to use straight away
- The cone is single-packed in a pouch that can be used to attach and detach the cone hygienically, which can also be used as a disposal bag for the used cone
- The water can be inserted either by gravity or by using the manual pump
- The manual pump has a non-return valve that prevents used water from running back in the pump

Shelf life

The expiry date is stated on the label

Storage

Store in a dry place with a temperature between 0° and 30° C, out of direct sunlight and away from children

Disposal

Qufora IrriSedo Cone does not require special disposal protocols and may be disposed of in household waste according to local guidelines and recommendations

Classification and sterilization

Qufora IrriSedo Cone is a Class I Device, non-sterile

Regulations and standards:

- MDR (Regulation 2017/745) - CE
- UK MDR 2002 - UKCA
- ISO 13485:2016 (certified)

Qufora IrriSedo Cone



Hydrophilic coated cone
Single-use cone is ready to use when dipped in water



Material description

Parts	Material	Softener
Cone		
Clear cone	TPE	No softener
Coating	PVP	No softener
Water bag		
Film	PVC, phthalate-free	DEHT/DOTP
Purple funnel/screw cap	PVC, phthalate-free/PE	DEHT/DOTP
Frosted tube	PVC, phthalate-free	DEHT/DOTP
Valve	PP (white part)/HDPE (purple part)	No softener
Pump	PVC, phthalate-free	DINCH
White NRV valve out and in	Hard PVC	No softener
Mesh for valve	Hard PVC	No softener
Black valve balls	Nitrile	No softener
Purple connector	Hard PVC	No softener
Extension tube		
Extension tube	PVC, phthalate-free	DEHT/DOTP
Purple connector	Hard PVC	No softener

Dimensions	Length	Diameter	Volume
Cone	75 mm	Tip is Ø8 mm	
Pump	170 mm	59 mm	90 ml
Water bag			1500 ml
Tube	100 cm	6.5/9,2 mm	

For more information, please visit www.qufora.com

Manufactured by:

Qufora A/S
Gydevang 28-30
3450 Allerød
Denmark

Tel: +45 88 300 592
Fax: +45 88 300 593
info@qufora.com
www.qufora.com

