

Connecting Tubes – Low Pressure

Non-leaking connection to standard luer lock connections

- Transparent soft tube
- Standard luer lock connections
- Wide range of lengths
- Maximum pressure for tubes 280 psi
- Maximum pressure for three-way stopcock 50 psi

Connecting Tubes – Low Pressure (Box of 25)

CATALOGUE NO.	DESCRIPTION
401004050	50 cm three-way stopcock/female-male, max pressure 50 psi
401011010	10 cm male-male luer lock, max pressure 280 psi
401011025	25 cm male-male luer lock, max pressure 280 psi
401012010	10 cm female-male luer lock, max pressure 280 psi
401012025	25 cm female-male luer lock, max pressure 280 psi
401012050	50 cm female-male luer lock, max pressure 280 psi
401012080	80 cm female-male luer lock, max pressure 280 psi
401013025	25 cm one-way stopcock/female-male luer lock, max pressure 280 psi
401013050	50 cm one-way stopcock/female-male luer lock, max pressure 280 psi
401013080	80 cm one-way stopcock/female-male luer lock, max pressure 280 psi

4010 11



4010 12



4010 13



8020 20

8020 21

802020000	Female/olive with stopper	(Box of 10)
802021000	Male/olive with stopper	