



International Scientific Supplies Ltd

## Product Specification

|                                       |                                                                                                                                                                                         |
|---------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Code                          | SC6002                                                                                                                                                                                  |
| Description                           | 60ml Clarified Polypropylene Container, Plastic Screw Cap, Patient Detail Label, Inner packs of 50                                                                                      |
| Manufacturer                          | International Scientific Supplies Ltd. Unit 6 Valley Road, Bradford BD1 4RU                                                                                                             |
| Image                                 |                                                                                                        |
| Material Body                         | Polypropylene Copolymer                                                                                                                                                                 |
| Material Cap                          | HDPE                                                                                                                                                                                    |
| Material Gasket (if applicable)       | NA                                                                                                                                                                                      |
| Food Contact                          | Polymers are in compliance with (EU) No.10/2011 on materials intended to come into contact with food. Full statements available separately on request.                                  |
| Primary Material Stewardships         | Available separately on request                                                                                                                                                         |
| Hygiene Level                         | Automated assembly under HEPA filtered airflow direct from moulding machine                                                                                                             |
| Quality control standard tested to    | ISO 6717:2021                                                                                                                                                                           |
| Leak Tested to                        | ISO 6717:2021                                                                                                                                                                           |
| 95 Kpa Leak Tested (for closure type) | Yes: Generically (closure and neck type) tested to: Test Method 49 CFR 178.605, IATA DGR 6.3.5. For a specific external packaging or label variation, certification on request at cost. |
| Storage                               | To be stored in original, undamaged packaging. Dry, at room temperature >0°C and <39°C                                                                                                  |
| Usage/Purpose                         | General IVD for Collection of Samples                                                                                                                                                   |
| CE Marked                             | Yes                                                                                                                                                                                     |
| IVD Classification                    | A                                                                                                                                                                                       |
| Basic Features                        |                                                                                                                                                                                         |
| Nominal Capacity (ml)                 | 60.0                                                                                                                                                                                    |
| Empty or Pre-filled                   | Empty                                                                                                                                                                                   |
| Autoclavability                       | Yes - Without Cap, 121 °C/2.1 bar                                                                                                                                                       |
| Centrifugation (RCF tested to)        | NA                                                                                                                                                                                      |
| Operational Temperature Range °C      | -20 to 80                                                                                                                                                                               |
| Chemical Resistance                   | See ISS Catalogue for general overview. Because applications may be infinitely variable, customer evaluation should be undertaken for use specific applications.                        |
| Expiry                                | See box label                                                                                                                                                                           |
| Dimensions (mm)                       |                                                                                                                                                                                         |
| Maximum Body Diameter (below thread)  | 38.8                                                                                                                                                                                    |
| Minimum Body Diameter (below thread)  | 38.4                                                                                                                                                                                    |
| Capped Height                         | 64.3                                                                                                                                                                                    |
| Un-capped Height                      | 61.2                                                                                                                                                                                    |

|                    |                   |
|--------------------|-------------------|
| Document Reference | ISSPEC: SC6002    |
| Issue Date         | 07-Dec-23         |
| Revision No.       | 2                 |
| Authorised By      | Andrew Littlewood |
| Position           | Managing Director |