

Product: TRANSFORMER 14,0 VDC

Reference code: 790500



1. General description

A transformer to be used for converting AC to DC. The transformer has separate insulated windings moulded in polyurethane and capsulated in plastic. It has a built in fuse and is electronically protected against short circuit.

The transformer has a mains cable (2 meters) with plug and a 1-meter cable with socket for transfer to a 12/24V 12 mm plug that fits plug on Cederroth heating cabinet for eye wash, REF 790400.

2. Intended use

To be used for stabilized DC power supply to Cederroth Eye Wash cabinet, Ref 790400.

3. Technical description

Product dimensions

(l x w x h) mm: 130x92x87
Weight (Kg) 1,7

Specifications

Input voltage: 230V \pm 6%
Frequency: 47-63 Hz
Output voltage: 14 VDC
Current: 2,2 A
Power: 30 W
Max.Ripple: 0.5% RMS
Efficiency: > 50%
Voltage adjustment: < 2,5%
According to: EN60065
Test/insulating voltage: 4,2 kV AC RMS
Construction class: II
Insulation class: B (130°C)
Ambient temperature (t_a): 25°C. At +40 °C reduce rated power with 15%
Degree of protection: IP44



PRODUCT SPECIFICATION

4. Composition

Consumer package

<u>Ref#</u>	<u>Product/Material</u>	<u>Pcs</u>
790500	Transformer 14,0 VDC	1

Transport package

Number of consumer packages in transport package:	1
Dimensions (l x w x h) mm:	255 x 110 x 105
Weight (kg):	2,0

5. Labeling

On product/ consumer package

Product name
Cederroth Reference code

On transport package

Product name
Cederroth Reference code

6. Storage conditions

The product should be stored in the original package for maximum protection until time of use.

Authorized by: Teija Ålander
Quality Assurance Manager

Date: 2009-06-16



www.firstaid.cederroth.com

Cederroth Industrial Products AB, Box 715, Kanalvägen 10A, SE 194 27 Upplands Väsby, Sweden.
Phone: +46 8 590 96 300, Fax: +46 8 590 30 953, E-mail: firstaid@cederroth.com