

DAMMSUGARPÅSAR PÖLYNIMURIPUSSEJA STØVSUGERPOSER VACUUM CLEANER BAGS TOLMUIMEJA KOTID МЕШКИ ДЛЯ ПЫЛЕСОСА

Passar till / Sopivat seuraaviin / Passer til / To fit

AEG

AirMax AAM 6100 → AAM 6299
Clario AEC 7570 → AEC 7572
OXY3 System AOS 9300 → AOS 9352
System Pro P1 → P999
Ultra Silencer AUS 4030, AUS 4040
Viva Control AVC 1110 → AVC 1190,
AVC 1220 → AVC 1230
Viva Quickstop AVQ 2100 → AVQ 2190

ELECTROLUX

AirMax ZAM 6100 → ZAM 6195
Bolido Z 4500 → Z 4595
Clario Z 1900 → Z 2095, Z 7510 → Z 7549
Ergo Space ZE 310, ZE 320, ZE 340, ZE 350 SC
ZE 2200 → ZE 2299, ZEG 300, XXL110, XXL130
XXL160, Excellio Z 5000 → Z 5695
Oxygen Z 5500 → Z 5995
Oxygen+ Z 7320 → Z 7399
OXY3 System ZO 6320 → ZO 6399
Smartvac Z 5000 → Z 5695
Ultra Silencer Z 3300 → Z 3395, ZCS 2100 Classic Silence
ZP 3510, ZUS 3932B, ZUSG 3000, ZUSG 3900
Ultraone Z 8800 → Z 8890

HUGIN

Titan HN 7005, HN 7010, HN 7015,
HN 7020, Tornado HN 8000

PHILIPS

City Line HR 8368 → HR 8399
City Line FC 8400 → FC 8499
Expression FC 8200 → FC 8219,
FC 8600 → FC 8649, HR 8300 → HR 8349
Impact FC 8380 → FC 8399, Impact HR 8350 → HR 8367
Jewel FC 9050 → 9079
Marathon FC 9200 → 9229
Mobilo HR 8500 → HR 8599, Milano, New York
Performer FC 9150 → FC 9179
Specialist FC 9100 → FC 9149, Sydney, Sydney +
HR 6999, Universe FC 9000 → FC 9049

TORNADO


Bolido 1500 → 1750, 4500 → 4559
Calypso TO 6310 → TO 6330,
TO 6510 → TO 6530
Essensio TO 4605 → TO 4625N
Modelys CA 6200 → CA 6230
Super Pro TO 30, TO 50 TO 55

VOLTA

AirMax U 3610, U 3620, U 3626, U 6410
U 6411, U 6416 U 6420, U 6426, U 6430
UC 6100 → UC 6199
Bolido U 4510 → U 4595
Control U 4610 → U 4640
Essensio U 5410, U 5420, U 5421
Jetmaxx U 68FD1, U6815SP, U 6820R
U 6820W, Maximus U 7510 → U 7540
Modelys U 6200 → U 6290
Quickstop U 4400 → U 4461, U 4602



3x



Art.nr

N 100

87013



Made in EU