

## Dräger Alcotest® 6820 Alcohol Screening Device

Keeping the roads safe and free of impaired drivers is an unpredictable and high stress job. Dräger designed the Alcotest® 6820 handheld breathalyzer specifically for the needs of law enforcement officers. It's easy to use and provides fast, reliable results in the toughest environments you face when every second matters.



## Benefits

---

### High-quality workmanship

A professional breath alcohol testing device must be able to withstand some abuse. The Alcotest 6820 new design and quality workmanship make this unit ideal for use in demanding conditions. Thanks to its durable material it is highly resistant to rough weather conditions such as cold or moisture, and it satisfies protection class IP 54.

---

### High user comfort

Testing intoxicated people requires a high degree of concentration. This is where the true value of an easy to operate device comes into play. All measurement functions are controlled with a single button. Easily understandable full-text messages on a large, backlit display guide you safely through the alcohol test. An LED display and acoustic signals support the visual display and report the completion of a test measurement. Two menu buttons are used for navigation and the collection of statistical data.

---

### Proven quality

Alcotest 6820 is also equipped with the proven electrochemical Dräger sensor. This sensor is characterised by very short response times coupled with precision and durability. Test results are always reliable regardless whether the temperature is -5 °C or +50 °C. Even with a high alcohol content, the sensor provides fast accurate results. And this is true for both active as well as passive measurements.

---

### Practical design

Alcotest 6820 offers a balanced, ergonomic design. Its compact form makes it especially easy to hold and operate with only one hand. The mouthpiece of the Alcotest 6820 unit is easily snapped into the holder even when it's dark thanks to its intuitive shape - regardless whether you are right-handed or left-handed or whether testing traffic moving on the right or left side of the road. The display is always in clear view. After use, the mouthpiece is just as easily and hygienically removed again.

---

### "Slide'n'Click" mouthpiece

The patented Dräger mouthpieces prevent any manipulation attempts. The optional return valve simultaneously ensures maximum hygiene. Alcotest 6820 uses the same reliable mouthpieces such as Alcotest models 6510 and 6810.

---

### Data processing and documentation

The expanded memory capacity of Alcotest 6820 is able to record up to 5000 test results. An optical interface enables wireless transmission of data to the Dräger mobile printer directly on site. Data is transferable to the PC via USB connection and the same connection can be used to configure the device.

## Benefits

---

### Optional accessories

A wide strap supports safe and comfortable use of the Alcotest 6820 testing device. The strap can be attached to your belt or around the wrist and secured with either buckles or hook and loop fastener. Reflectors make it easier to locate the device in the dark.

## Accessories



### Mouthpieces (Slide'n'click)

Mouthpieces are supplied in packs of 100, 250 and 1,000 with and without non-return valve.



### Power supply

Alkaline batteries or set of rechargeable batteries for 6820

## Accessories



### Leather pouch

Leather pouch in black or yellow for belt fastening



### Printer

Dräger Mobile Printer prints breath alcohol and drug test measurement results without using a dedicated power supply. Operates on 4 AA batteries.

## Related Products



### Dräger Alcotest® 5510

As entry level model of the successful Dräger Alcotest® 6510 the Dräger Alcotest® 5510 offers professional users precise and quick breath alcohol analysis in a user-friendly and compact form. Thanks to its wide range of possible configurations, the handheld instrument can be easily adapted to meet different international regulations and guidelines.

## Related Products

ST-15093-2008



### Dräger Alcotest® 7510

This compact and robust handheld breath alcohol measuring device is especially designed for advanced screening applications. Ideal for us by police, commerce and industry as an alcohol screening device. The Alcotest 7510 can in many countries and markets be used as an evidential device.

D-54720-2012



### Dräger DrugTest® 5000

No pipetting, no drips, no timing: Collecting an oral fluid sample is quick and easy with the Dräger DrugTest® 5000. The collected sample can then be analysed immediately for accurate results on the spot.

ST-19226-2007



### Dräger DCD 5000

Simple, fast and secure detection of intoxicants and drugs: The Dräger DCD 5000 does not only enable an easy collection of saliva, you can also store the samples and send them to the laboratory for analysis – without the sample being falsified along the way.

D-98736-2013



### Dräger Interlock® 7000

The Dräger Interlock® 7000 is an alcohol ignition interlock device. After a breath alcohol measurement it prevents a drunk driver from starting the vehicle. The Interlock® 7000 is very quickly ready for use. Additionally, the device can be equipped with a camera and/or a GPRS module, according to the specific customer requirements.

## Technical Data

Test method	Electrochemical Dräger sensor for 1/4" technology; alcohol-specific
Test range	0 to 2.5 mg/L; display indication when exceeding test range
Sampling	Standard: automatic sampling when minimum volume is reached Passive sampling or manual triggering of sampling possible
Ready for use	Approx. 2 s after powering up
Test result display	Approx. 3 s (with 0 mg/l), 10 s (at 0.5 mg/l, room temperature)
Operating temperature	-5 to +50 °C; -4 to +122 °F
Display	Graphic LCD display with background illumination; 41 mm x 24 mm (128 x 64 pixels)
LED	3 colours to indicate messages or alerts
Acoustic alarms	Different signal tones indicate various messages and alerts
Memory	Space for saving the last 5000 tests with test number, date and time
Power supply	Two AA batteries or NiMH batteries, battery indicator on the display. Around 1500 breath tests can be conducted with one set of batteries. Charging rechargeable NiMH batteries is possible in device
Calibration	Wet gas or dry gas calibration
Dimensions (H x W x D), weight	147 mm x 65 mm x 39 mm, approx. 260g
Device configuration	Device settings configurable directly via device menu (PIN required). No additional PC software required
Vibration and impact	Meets EN 60068-2-6, EN 60068-2-27, EN 60068-2-64, MIL-STD 810F
CE marking	Directive 89/336/EEC (electromagnetic compatibility)
Data interfaces	USB to PC; optical interface for printer control
Standard	Meets EN 15964
Protection type	IP 54

## Ordering Information

Dräger Alcotest® 6820 (test unit, 3 mouthpieces, 2 batteries, hand strap, plastic case)	83 22 660
Dräger Alcotest mouthpiece (Slide'n'click)	
Package with 100 pieces	68 10 690
Package with 250 pieces	68 10 825
Package with 1000 pieces	68 10 830
Dräger Alcotest mouthpiece (Slide'n'click) with return valve	
Package with 100 pieces	68 11 055
Package with 250 pieces	68 11 060
Package with 1000 pieces	68 11 065
PSU (power source) 600 mA, 11 V, for charging NiMH batteries	83 16 991
12 V vehicle adaptor for charging NiMH batteries	83 20 252
PC connection cable for Dräger Alcotest Screener USB	83 19 715

## Notes

## Notes

Dräger Marine & Offshore  
Beurtschipperstraat 1  
3194 DK Hoogvliet  
+31 (0)10 295 2740  
sales-mo.sd.nl@draeger.com  
www.draeger-mo.com



### CORPORATE HEADQUARTERS

Drägerwerk AG & Co. KGaA  
Moislinger Allee 53–55  
23558 Lübeck, Germany  
www.draeger.com

### REGION EUROPE CENTRAL AND EUROPE NORTH

Dräger Safety AG & Co. KGaA  
Revalstraße 1  
23560 Lübeck, Germany  
Tel +49 451 882 0  
Fax +49 451 882 2080  
info@draeger.com

### REGION EUROPE SOUTH

Dräger Safety France SAS  
25, rue Georges Besse  
92182 Antony Cedex  
Tel +33 1 46 11 56 00  
Fax +33 1 40 96 97 20  
europe.south@draeger.com

### REGION MIDDLE EAST, AFRICA

Dräger Safety AG & Co. KGaA  
Branch Office  
P.O. Box 505108  
Dubai, United Arab Emirates  
Tel +971 4 4294 600  
Fax +971 4 4294 699  
contactuae@draeger.com

### REGION ASIA PACIFIC

Draeger Safety Asia Pte Ltd  
25 International Business Park  
#04-20/21 German Centre  
Singapore 609916  
Tel +65 6308 9400  
Fax +65 6308 9401  
asia.pacific@draeger.com

### REGION CENTRAL AND SOUTH AMERICA

Dräger Panama S. de R.L.  
Complejo Business Park,  
V tower, 10th floor  
Panama City  
Tel +507 377 9100  
Fax +507 377 9130  
contactcsa@draeger.com

Locate your Regional  
Sales Representative at:  
www.draeger.com/contact

