

































	Benämning	ANSI	Volt (V)	Watt (W)	Socket	Ljusflöde (Lumen)	L (mm)	d (mm)	a (mm)	Brinntid (h)	Bild
6470165	64222		6	10	PG22	150	44,0	9,0	14,0	300	
6436004	64223	M/43	6	10	G4	150	38,0	9,0	24,0	300	
6435865	64225	ESA	6	10	G4	200	31,0	9,0	19,5	100	
6435634	HLX64250	ESB	6	20	G4	480	31,0	9,0	19,5	100	
6435639	HLX64251		6	20	PG22	500	40,0	9,0	14,0	100	
6480092	5971 / Ph		6	30	G4	-	-	-	-	-	
6435519	64275		6	35	G4	780	40,0	9,0	26,0	50	
6435998	64260		12	30	PG22	800	40,0	9,0	14,0	50	
6435642	64261		12	30	G6,35	750	44,0	11,5	30,0	50	

Artikel nr	Benämning	ANSI	Volt (V)	Watt (W)	Socket	Ljusflöde (Lumen)	L (mm)	d (mm)	a (mm)	Brinntid (h)	Bild
6470486	HLX64609		12	50	PG22	1550	48,0	11,5	18,0	50	
6435832	HLX64610	BRL	12	50	G6,35	1600	44,0	11,5	30,0	50	
6436244	HLX64611		12	50	G6,35	1350	44,0	11,5	30,0	100	
6435006	HLX64616		12	75	G4	2350	35,0	-	27,0	25	
6470448	HLX64621		12	100	PG22	2750	48,0	11,5	18,0	2000	
6435709	HLX62138		12	100	GZ6,35	-	-	-	-	-	
6435683	HLX64623	EVA	12	100	GY6,35	2800	44,0	11,5	30,0	2000	
6435840	HLX64625	FCR	12	100	GY6,35	3600	44,0	11,5	30,0	50	
6435669	HLX64626	EHE	12	100	PG22	3600	48,0	11,5	18,0	50	

Artikel nr	Benämning	ANSI	Volt (V)	Watt (W)	Socket	Ljusflöde (Lumen)	L (mm)	d (mm)	a (mm)	Brinntid (h)	Bild
6436780	64628	FDT	12	100	GY9,5	3000	57,0	13,0	27,0	50	
6435964	HLX64633	BRJ	15	150	G6,35	5600	44,0	11,5	30,0	50	
6435796	64650		22,8	50	G6,35	1000	44,0	13,0	30,0	1300	
6435740	HLX64638		24	100	G6,35	2900	50,0	13,0	32,0	300	
6435972	HLX64640	FCS	24	150	G6,35	6000	50,0	13,5	32,0	50	
6435691	HLX64642	FDV	24	150	G6,35	5000	50,0	13,5	32,0	300	
6436269	64643	FDS	24	150	GY9,5	5000	57,0	15,0	34,1	100	
---	HLX64654		24	250	GY9,5	9000	88,0	13,5	35,0	300	

Artikel nr	Benämning	ANSI	Volt (V)	Watt (W)	Socket	Ljusflöde (Lumen)	L (mm)	d (mm)	a (mm)	Brinntid (h)	Bild
6435782	HLX64655	EHJ	24	250	G6,35	10000	55,0	13,5	33,0	50	
6435792	HLX64656	FNT	24	275	G6,35	9000	55,0	13,5	33,0	75	
6435667	HLX64657	EVC	24	250	G6,35	10000	55,0	13,5	33,0	300	
6435758	HLX64663	EVD	36	400	G6,35	16000	60,0	16,0	36,0	50	
6435675	HLX64664	EVD	36	400	G6,35	14500	57,0	18,0	36,0	150	
6435725	HLX64665		36	400	G6,35	12200	60,0	18,0	36,0	300	
---	HLX64669	GCD	50	590	GY9,5	21500	70,0	19,0	41,3	50	