

# VICRYL\*

(Polyglactin 910) Braided and Monofilament

## SUTURE

|                     |                   |   |
|---------------------|-------------------|---|
| <b>Description:</b> | <b>Braided</b>    | For easy handling and secure knot tying.                  |
|                     | <b>Coated</b>     | For smooth passage through tissue and easy knot tie down. |
|                     | <b>Synthetic</b>  | For minimal tissue reaction.                              |
|                     | <b>Absorbable</b> | By hydrolysis. Essentially complete in 56-70 days.        |

|                          |                          |  |
|--------------------------|--------------------------|--|
| <b>Tensile strength:</b> | <b>Post implantation</b> | <b>Approximate % original strength remaining</b> |
|                          | 14 days                  | 75%  |
|                          | 21 days                  | 50% (6-0 and larger)<br>40% (7-0 and smaller)    |
|                          | 28 days                  | 25% (6-0 and larger)                             |

**Color:** Violet or undyed.

**Range:** 10-0 to 2 (USP). Supplied as needed sutures and ligatures. Sizes 10-0 and 9-0 are monofilament in structure.












**Indications:** VICRYL\* sutures are intended for use in soft tissue approximation and/or ligation, including use in ophthalmic surgery, peripheral nerve adaptation and microsurgery for vessels less than 2 mm in diameter.

Typical areas of use include:

- Fascia closure - due to the unique 28-day claim
- Subcutaneous fat
- Joint capsule
- Uterus

Full details in the Instruction for Use included in every package.








| 1/2 Circle Taper Point Needles   |       |       |             |                   |                |         |  |
|--|-------|-------|-------------|-------------------|----------------|---------|--|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code    |  |
|  TF-6<br>6,5 mm   | 8-0   | ●     | 30          |                   | 12             | V1027G  |  |
|  | 7-0   | ●     | 30          |                   | 36             | V1028H  |  |
|  TF-1<br>10 mm  | 5-0   | ●     | 70          |                   | 36             | V133H   |  |
|  RB-2<br>13 mm  | 6-0   | ●     | 70          |                   | 36             | PZ2571H |  |
|  TF<br>13 mm  | 6-0   | ●     | 70          |                   | 36             | V926H   |  |
|  | 5-0   | ●     | 70          |                   | 36             | V925H   |  |
|  | 4-0   | ●     | 70          |                   | 36             | V924H   |  |
|  RB-1<br>17 mm  | 6-0   | ●     | 70          |                   | 36             | V302H   |  |
|  | 5-0   | ●     | 70          |                   | 36             | V303H   |  |
|  | 5-0   | ○     | 70          |                   | 36             | V213H   |  |
|  | 4-0   | ●     | 70          |                   | 36             | V304H   |  |
|  | 4-0   | ○     | 70          |                   | 36             | V214H   |  |
|  | 4-0   | ●     | 8x45        | CONTROL RELEASE*  | 24             | V734E   |  |
|  | 4-0   | ●     | 4x45        | CONTROL RELEASE*  | 12             | V735G   |  |
|  | 4-0   | ●     | 8x70        | CONTROL RELEASE*  | 24             | V799E   |  |
|  | 3-0   | ●     | 70          |                   | 36             | V305H   |  |
|  | 3-0   | ○     | 70          |                   | 36             | V215H   |  |
|  | 3-0   | ●     | 8x45        | CONTROL RELEASE*  | 12             | J713D   |  |
| 2-0  | ●     | 70    |             | 36                | V306H          |         |  |
|  RB-1 RB-1<br>17 mm   | 3-0   | ●     | 70          |                   | 36             | V667H   |  |
|  JRB-1<br> VISI-BLACK<br>17 mm | 5-0   | ●     | 70          | VISI-BLACK*       | 36             | V3030H  |  |
|  | 4-0   | ●     | 70          | VISI-BLACK*       | 36             | V3040H  |  |
|  SH-1<br>22 mm  | 4-0   | ●     | 70          |                   | 36             | V310H   |  |
|  | 4-0   | ○     | 70          |                   | 36             | V426H   |  |
|  | 3-0   | ●     | 70          |                   | 36             | V311H   |  |
|  | 3-0   | ○     | 70          |                   | 36             | V219H   |  |
|  | 3-0   | ●     | 4x45        | CONTROL RELEASE*  | 36             | V782H   |  |
|  | 2-0   | ●     | 70          |                   | 36             | V312H   |  |
|  | 2-0   | ○     | 70          |                   | 36             | V220H   |  |
|  | 2-0   | ●     | 8x45        | CONTROL RELEASE*  | 24             | V792E   |  |
|  JB-1<br> VISI-BLACK<br>22 mm  | 4-0   | ●     | 70          | VISI-BLACK*       | 36             | V3100H  |  |
|  | 3-0   | ●     | 70          | VISI-BLACK*       | 36             | V3110H  |  |
|  | 2-0   | ●     | 70          | VISI-BLACK*       | 36             | V3120H  |  |





**VICRYL\***  
(Polyglactin 910) Braided and Monofilament


|  1/2 Circle Taper Point Needles |       |       |             |                   |                |         |
|--|-------|-------|-------------|-------------------|----------------|---------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code    |
|  SH<br>26 mm                    | 4-0   | ●     | 70          |                   | 36             | V315H   |
|  | 4-0   | ●     | 8x70        | CONTROL RELEASE*  | 12             | V783G   |
|  | 3-0   | ●     | 70          |                   | 36             | V316H   |
|  | 3-0   | ○     | 70          |                   | 36             | V416H   |
|  | 3-0   | ●     | 90          |                   | 36             | V242H   |
|  | 3-0   | ●     | 4x45        | CONTROL RELEASE*  | 36             | V780H   |
|  | 3-0   | ●     | 8x45        | CONTROL RELEASE*  | 12             | J774D   |
|  | 3-0   | ●     | 8x70        | CONTROL RELEASE*  | 12             | J784D   |
|  | 2-0   | ●     | 70          |                   | 36             | V317H   |
|  | 2-0   | ○     | 70          |                   | 36             | V224H   |
|  | 2-0   | ●     | 90          |                   | 36             | V243H   |
|  | 2-0   | ●     | 8x45        | CONTROL RELEASE*  | 12             | J775D   |
|  | 0     | ●     | 70          |                   | 36             | V318H   |
|  | 0     | ○     | 70          |                   | 36             | V225H   |
|  JB<br>VISI-BLACK<br>26 mm      | 4-0   | ●     | 70          | VISI-BLACK*       | 36             | V3150H  |
|  | 3-0   | ●     | 70          | VISI-BLACK*       | 36             | V3160H  |
|  | 3-0   | ○     | 70          | VISI-BLACK*       | 36             | V4416H  |
|  | 2-0   | ●     | 70          | VISI-BLACK*       | 36             | V3170H  |
|  MH-1<br>31 mm                 | 3-0   | ●     | 70          |                   | 36             | V245H   |
|  | 2-0   | ●     | 70          |                   | 36             | V246H   |
|  | 0     | ●     | 70          |                   | 36             | V247H   |
|  MH<br>36 mm                  | 4-0   | ●     | 90          |                   | 36             | PG2592H |
|  | 3-0   | ●     | 70          |                   | 36             | V322H   |
|  | 3-0   | ●     | 90          |                   | 36             | V100H   |
|  | 2-0   | ●     | 70          |                   | 36             | V323H   |
|  | 2-0   | ○     | 70          |                   | 36             | V226H   |
|  | 2-0   | ●     | 90          |                   | 36             | V101H   |
|  | 0     | ●     | 70          |                   | 36             | V324H   |
|  | 0     | ●     | 90          |                   | 36             | V102H   |
|  | 1     | ●     | 70          |                   | 36             | V325H   |
|  | 1     | ○     | 70          |                   | 36             | V228H   |
|  LH<br>40 mm                  | 2-0   | ●     | 70          |                   | 36             | PH2574H |





|  1/2 Circle Taper Point Needles (Heavier Wire Diameter) |       |       |             |                   |                |           |
|--|-------|-------|-------------|-------------------|----------------|-----------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code      |
|  UCL<br>13 mm   | 3-0   | ●     | 70          |                   | 36             | V113H     |
|  | 0     | ●     | 70          |                   | 36             | V115H     |
|  UCLX<br>16 mm  | 3-0   | ●     | 70          |                   | 36             | V13H      |
|  | 2-0   | ●     | 70          |                   | 36             | V14H      |
|  | 0     | ●     | 70          |                   | 36             | V15H      |
|  | 1     | ●     | 70          |                   | 36             | V16H      |
|  CT-3<br>22 mm  | 3-0   | ●     | 70          |                   | 36             | V327H     |
|  | 2-0   | ●     | 70          |                   | 36             | V328H     |
|  | 0     | ●     | 70          |                   | 36             | V329H     |
|  CT-2<br>26 mm  | 3-0   | ●     | 70          |                   | 36             | V332H     |
|  | 2-0   | ●     | 70          |                   | 36             | V333H     |
|  | 2-0   | ○     | 70          |                   | 36             | V289H     |
|  | 2-0   | ●     | 4x45        | CONTROL RELEASE*  | 24             | V7842E    |
|  | 0     | ●     | 70          |                   | 36             | V334H     |
|  | 0     | ○     | 70          |                   | 36             | V270H     |
|  | 0     | ●     | 8x45        | CONTROL RELEASE*  | 24             | V744E     |
|  | 0     | ●     | 4x70        | CONTROL RELEASE*  | 24             | 4PK2575YE |
|  | 1     | ●     | 70          |                   | 36             | V335H     |
|  | 2     | ●     | 70          |                   | 36             | V336H     |
|  CT-1<br>36 mm  | 3-0   | ●     | 70          |                   | 36             | V338H     |
|  | 3-0   | ○     | 90          |                   | 36             | V944H     |
|  | 2-0   | ●     | 70          |                   | 36             | V339H     |
|  | 2-0   | ●     | 90          |                   | 36             | V345H     |
|  | 2-0   | ○     | 90          |                   | 36             | V945H     |
|  | 2-0   | ○     | 8x70        | CONTROL RELEASE*  | 12             | J742D     |
|  | 0     | ●     | 70          |                   | 36             | V340H     |
|  | 0     | ●     | 90          |                   | 36             | V346H     |
|  | 0     | ○     | 90          |                   | 36             | V946H     |
|  | 0     | ●     | 8x45        | CONTROL RELEASE*  | 12             | J740D     |
|  | 1     | ●     | 70          |                   | 36             | V341H     |
|  | 1     | ●     | 90          |                   | 36             | V347H     |
|  | 1     | ●     | 4x70        | CONTROL RELEASE*  | 12             | V736G     |
|  | 2     | ●     | 90          |                   | 36             | V348H     |
| 2  | ○     | 90    |             | 36                | V948H          |           |
|  MO-4<br>36 mm  | 0     | ●     | 70          |                   | 36             | V436H     |
|  | 1     | ●     | 90          |                   | 36             | V255H     |

**VICRYL\***  
(Polyglactin 910) Braided and Monofilament



|  <b>1/2 Circle Taper Point Needles (Heavier Wire Diameter)</b> |  |       |             |                   |                |           |
|---|--|-------|-------------|-------------------|----------------|-----------|
| Needle  | Gauge  | Color | Length (cm) | Other information | Number per box | Code      |
| <br>CT<br>40 mm  | 3-0  | ●     | 70          |                   | 36             | V350H     |
|   | 2-0  | ●     | 70          |                   | 36             | V351H     |
|   | 2-0  | ●     | 8x45        | CONTROL RELEASE*  | 12             | 8PM2544YG |
|   | 0  | ●     | 70          |                   | 36             | V352H     |
|   | 0  | ●     | 90          |                   | 36             | V358H     |
|   | 0  | ●     | 150         | LOOP              | 24             | V1407E    |
|   | 1  | ●     | 70          |                   | 36             | V353H     |
|   | 1  | ●     | 90          |                   | 36             | V359H     |
|   | 1  | ●     | 8x45        | CONTROL RELEASE*  | 12             | J753D     |
|   | 2  | ●     | 90          |                   | 36             | V360H     |
|   | 2  | ○     | 90          |                   | 36             | V960H     |
|   | <br>CTX<br>48 mm | 3-0   | ●           | 70                |                | 36        |
| 2-0   |  | ●     | 70          |                   | 36             | V363H     |
| 0   |  | ●     | 70          |                   | 36             | V364H     |
| 0   |  | ●     | 90          |                   | 36             | V370H     |
| 0   |  | ○     | 90          |                   | 36             | V170H     |
| 0   |  | ●     | 8x45        | CONTROL RELEASE*  | 12             | J764D     |
| 1   |  | ●     | 70          |                   | 36             | V365H     |
| 1   |  | ●     | 90          |                   | 36             | V371H     |
| 1   |  | ○     | 90          |                   | 36             | V366H     |
| 1   |  | ●     | 8x45        | CONTROL RELEASE*  | 12             | J765D     |
| 2   |  | ●     | 90          |                   | 36             | V372H     |
| 2   |  | ○     | 90          |                   | 36             | V367H     |
| <br>TP-1<br>65 mm  |  | 2     | ●           | 4x70              |                | 6         |
| <br>XLH<br>70 mm   | 2-0  | ●     | 70          |                   | 12             | V581G     |
|   | 0  | ●     | 70          |                   | 12             | V582G     |
|   | 1  | ●     | 70          |                   | 12             | V583G     |


| 1/2 Circle ETHIGUARD* Blunt Point Needles   |       |       |             |                   |                |       |
|---|-------|-------|-------------|-------------------|----------------|-------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code  |
| <br>MHB-1<br>31 mm | 3-0   | ●     | 75          |                   | 12             | W9983 |
|   | 2-0   | ●     | 75          |                   | 12             | W9984 |
| <br>CTB-1<br>36 mm | 2-0   | ●     | 75          |                   | 12             | W9985 |
|   | 2-0   | ●     | 75          | Heavy Needle      | 12             | W9993 |
|   | 0     | ●     | 75          |                   | 12             | W9986 |
|   | 0     | ●     | 90          | Heavy Needle      | 12             | W9994 |
|   | 1     | ●     | 90          | Heavy Needle      | 12             | W9995 |
| <br>CTB<br>40 mm   | 0     | ●     | 75          |                   | 12             | W9988 |
|   | 0     | ●     | 90          | Heavy Needle      | 12             | W9996 |
|   | 1     | ●     | 90          | Heavy Needle      | 12             | W9997 |
| <br>CTXB<br>48 mm  | 0     | ●     | 90          |                   | 12             | W9990 |
|   | 1     | ●     | 90          |                   | 12             | W9991 |


| 3/8 Circle Blunt Point Needles   |       |       |             |                   |                |       |
|--|-------|-------|-------------|-------------------|----------------|-------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code  |
| <br>BP-5<br>65 mm | 1     | ●     | 100         |                   | 12             | W9391 |

| 5/8 Circle Taper Point Needles  |       |       |             |                   |                |          |
|---|-------|-------|-------------|-------------------|----------------|----------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code     |
| <br>UR-6<br>26 mm      | 3-0   | ●     | 70          |                   | 36             | V601H    |
|   | 2-0   | ●     | 70          |                   | 36             | V602H    |
|   | 0     | ●     | 70          |                   | 36             | V603H    |
|   | 1     | ●     | 70          |                   | 36             | VC2575H  |
| <br>UR-6 UR-6<br>26 mm | 2-0   | ●     | 70          |                   | 36             | VCC2573H |
| <br>UR-5<br>36 mm      | 2-0   | ●     | 70          |                   | 36             | V375H    |
|   | 0     | ●     | 70          |                   | 36             | V376H    |
|   | 1     | ●     | 70          |                   | 36             | V377H    |
| <br>UR-4<br>40 mm      | 2-0   | ●     | 70          |                   | 36             | V380H    |
|   | 0     | ●     | 70          |                   | 36             | V381H    |

| ▼ 1/2 Circle TAPERCUT* Needles  |       |       |             |                   |                |      |          |
|---|-------|-------|-------------|-------------------|----------------|------|----------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code |          |
|  V-37  | 40 mm | 2-0   | ●           | 90                |                | 36   | VS4020H  |
|   |       | 0     | ●           | 90                |                | 36   | VS4000H  |
|  V-37  | 40 mm | 1     | ●           | 70                |                | 36   | ODD2574H |
|  V-40  | 48 mm | 2-0   | ●           | 90                |                | 36   | VS5020H  |
|   |       | 0     | ●           | 70                |                | 36   | VS5000H  |
|   |       | 1     | ●           | 150               | LOOP           | 24   | V829E    |
|  BPT-1 | 48 mm | 6     | ●           | 75                |                | 12   | V140G    |
|   |       | 6     | ●           | 150               |                | 12   | OH2528G  |



| ▼ 3/8 Circle TAPERCUT* Needles  |       |       |             |                   |                |      |       |
|---|-------|-------|-------------|-------------------|----------------|------|-------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code |       |
|  V-18 | 13 mm | 6-0   | ●           | 70                |                | 36   | V991H |
|   |       | 5-0   | ●           | 70                |                | 36   | V990H |
|  V-4 | 17 mm | 4-0   | ○           | 70                |                | 12   | V240G |
|   |       | 4-0   | ○           | 70                |                | 36   | V240H |




| ▼ 5/8 Circle TAPERCUT* Needles  |       |       |             |                   |                |      |       |
|---|-------|-------|-------------|-------------------|----------------|------|-------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code |       |
|  UW-10 | 10 mm | 6-0   | ●           | 30                |                | 12   | W9172 |




| ▼ Compound Curve TAPERCUT* Needles   |       |       |             |                   |                |      |        |
|--|-------|-------|-------------|-------------------|----------------|------|--------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code |        |
|  DA<br>VISI-BLACK | 25 mm | 4-0   | ●           | 45                | VISI-BLACK*    | 12   | 18531G |

# VICRYL\*

(Polyglactin 910) Braided and Monofilament

| ● Fish Hook Needles   |       |       |             |                   |                |         |
|---|-------|-------|-------------|-------------------|----------------|---------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code    |
| <br>PB-30<br>30 mm | 2-0   | ●     | 70          | Taper point       | 36             | DF2570H |
|   | 1     | ●     | 70          | Taper point       | 36             | DF2573H |
| <br>V-38<br>31 mm  | 1     | ●     | 75          | TAPERCUT*         | 12             | W9335   |

| ● Straight Taper Point Needles   |       |       |             |                   |                |         |
|--|-------|-------|-------------|-------------------|----------------|---------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code    |
| <br>ST-4<br>19 mm           | 4-0   | ●     | 70          |                   | 36             | BA2573H |
|  | 3-0   | ●     | 70          |                   | 36             | BA2574H |
| <br>ST-4<br>ST-4<br>19 mm | 4-0   | ●     | 35          |                   | 36             | V620H   |
| <br>ST<br>48 mm           | 3-0   | ●     | 70          |                   | 36             | BC2573H |









| ▼ 1/2 Circle TAPERCUT* Needles   |       |       |             |                   |                |           |
|--|-------|-------|-------------|-------------------|----------------|-----------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code      |
| <br>V-5<br>17 mm  | 4-0   | ●     | 70          |                   | 12             | V994G     |
|  | 4-0   | ●     | 70          |                   | 36             | V994H     |
|  | 4-0   | ○     | 70          |                   | 36             | V230H     |
|  | 3-0   | ●     | 70          |                   | 36             | V276H     |
| <br>V-7<br>26 mm  | 3-0   | ●     | 70          |                   | 12             | V998G     |
|  | 3-0   | ●     | 70          |                   | 36             | V998H     |
|  | 2-0   | ●     | 70          |                   | 36             | V999H     |
|  | 2-0   | ●     | 6x45        | CONTROL RELEASE*  | 24             | 6OB2545YE |
|  | 0     | ●     | 70          |                   | 36             | V279H     |
| <br>V-34<br>36 mm | 3-0   | ●     | 90          |                   | 36             | V516H     |
|  | 2-0   | ●     | 90          |                   | 36             | V517H     |
|  | 0     | ●     | 90          |                   | 36             | V518H     |
|  | 1     | ●     | 90          |                   | 36             | V519H     |
|  | 1     | ○     | 90          |                   | 36             | V919H     |





**VICRYL\***  
(Polyglactin 910) Braided and Monofilament

| ▼ 1/2 Circle Reverse Cutting Needles (Heavier Wire Diameter)                            |       |       |             |                   |                 |      |         |
|---|-------|-------|-------------|-------------------|-----------------|------|---------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box  | Code |         |
|  X-1   | 22 mm | 3-0   | ●           | 70                |                 | 36   | V460H   |
|   |       | 3-0   | ○           | 70                |                 | 36   | ME2673H |
|   |       | 2-0   | ●           | 70                |                 | 36   | V461H   |
|   |       | 2-0   | ○           | 75                |                 | 36   | JV459   |
|  OS-4  | 22 mm | 0     | ○           | 70                | HEAVY NEEDLE    | 36   | V694H   |
|   |       | 2     | ●           | 75                | HEAVY NEEDLE    | 12   | W9287   |
|  CP-2  | 26 mm | 3-0   | ●           | 70                |                 | 36   | MF2572H |
|   |       | 2-0   | ○           | 70                |                 | 36   | V869H   |
|   |       | 0     | ●           | 70                |                 | 36   | MF2574H |
|   |       | 0     | ●           | 4x45              | CONTROL RELEASE | 24   | V870E   |
|   |       | 1     | ○           | 70                |                 | 36   | MF2675H |
|  CP-1  | 36 mm | 3-0   | ●           | 70                |                 | 36   | V465H   |
|   |       | 2-0   | ●           | 70                |                 | 36   | V466H   |
|   |       | 2-0   | ●           | 90                |                 | 36   | V472H   |
|   |       | 2-0   | ○           | 90                |                 | 36   | JV1472  |
|   |       | 0     | ●           | 70                |                 | 36   | V467H   |
|   |       | 0     | ●           | 90                |                 | 36   | V473H   |
|   |       | 0     | ●           | 4x45              | CONTROL RELEASE | 12   | V475G   |
|   |       | 1     | ●           | 70                |                 | 36   | V468H   |
|   |       | 1     | ●           | 90                |                 | 36   | V474H   |
|   |       | 2     | ●           | 90                |                 | 36   | V482H   |
|  CP  | 40 mm | 2-0   | ●           | 70                |                 | 36   | V478H   |
|   |       | 0     | ●           | 70                |                 | 36   | V479H   |
|   |       | 0     | ●           | 90                |                 | 36   | V485H   |
|   |       | 1     | ●           | 70                |                 | 36   | V480H   |
|   |       | 1     | ●           | 90                |                 | 36   | V486H   |
|  CPX | 48 mm | 0     | ●           | 90                |                 | 36   | V1057H  |
|   |       | 1     | ●           | 90                |                 | 36   | V1058H  |
|   |       | 2     | ●           | 90                |                 | 36   | V1059H  |

| ▼ 1/2 Circle Reverse Cutting PRIME* Needles  |       |       |             |                   |                |      |         |
|--|-------|-------|-------------|-------------------|----------------|------|---------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code |         |
|  PS-4 | 16 mm | 5-0   | ○           | 45                | Compound curve | 12   | W9436   |
|  |       | 4-0   | ○           | 45                | MULTIPASS*     | 36   | MPV507H |
|  |       | 4-0   | ○           | 45                |                | 12   | V507G   |
|  |       | 4-0   | ○           | 45                | Compound curve | 12   | W9437   |





| ▼ 3/8 Circle Reverse Cutting PRIME* Needles   |       |       |             |                   |                |      |          |
|---|-------|-------|-------------|-------------------|----------------|------|----------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code |          |
|  P-1     | 11 mm | 6-0   | ○           | 45                | MULTIPASS*     | 36   | MPV489H  |
|   |       | 6-0   | ○           | 45                |                | 36   | V489H    |
|   |       | 5-0   | ○           | 45                | MULTIPASS*     | 36   | MPV490H  |
|   |       | 5-0   | ○           | 45                |                | 36   | V490H    |
|  P-3     | 13 mm | 6-0   | ○           | 45                | MULTIPASS*     | 36   | MPV492H  |
|   |       | 6-0   | ○           | 45                |                | 36   | V492H    |
|   |       | 5-0   | ○           | 45                | MULTIPASS*     | 36   | MPV493H  |
|   |       | 5-0   | ○           | 45                |                | 36   | V493H    |
|   |       | 4-0   | ○           | 45                | MULTIPASS*     | 36   | MPV494H  |
|   |       | 4-0   | ○           | 45                |                | 36   | V494H    |
|  PS-3    | 16 mm | 5-0   | ○           | 45                | MULTIPASS*     | 36   | MPV500H  |
|   |       | 4-0   | ○           | 45                |                | 24   | W9508T   |
|  PS-2    | 19 mm | 5-0   | ○           | 45                | MULTIPASS*     | 36   | MPV495H  |
|   |       | 4-0   | ○           | 45                | MULTIPASS*     | 36   | MPV496H  |
|   |       | 4-0   | ○           | 45                |                | 24   | W9515T   |
|   |       | 3-0   | ○           | 45                | MULTIPASS*     | 36   | MPV497H  |
|   |       | 3-0   | ○           | 45                |                | 36   | V497H    |
|  PS-2 S | 19 mm | 4-0   | ○           | 45                | Slimmed        | 36   | V496H    |
|  PS-1  | 24 mm | 3-0   | ○           | 45                | MULTIPASS*     | 36   | MPV683H  |
|   |       | 3-0   | ○           | 45                |                | 36   | V683H    |
|   |       | 2-0   | ○           | 45                | MULTIPASS*     | 36   | MPV684H  |
|   |       | 2-0   | ○           | 45                |                | 36   | V684H    |
|  PS    | 26 mm | 3-0   | ○           | 70                | MULTIPASS*     | 36   | MPV9526H |
|  PSL   | 30 mm | 2-0   | ●           | 70                |                | 36   | V686H    |



| ▼ 3/8 Circle Reverse Cutting Needles   |       |       |             |                   |                |      |       |
|--|-------|-------|-------------|-------------------|----------------|------|-------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code |       |
|  C-3  | 13 mm | 6-0   | ●           | 45                |                | 36   | V384H |
|  |       | 5-0   | ●           | 45                |                | 36   | V385H |
|  |       | 4-0   | ●           | 45                |                | 36   | V386H |
|  FS-3 | 16 mm | 6-0   | ●           | 45                |                | 36   | V387H |
|  |       | 5-0   | ●           | 45                |                | 36   | V388H |



**VICRYL\***  
(Polyglactin 910) Braided and Monofilament


| ▼ 3/8 Circle Reverse Cutting Needles   |       |       |             |                   |                |        |
|--|-------|-------|-------------|-------------------|----------------|--------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code   |
|  FS-2<br>19 mm  | 5-0   | ○     | 45          |                   | 36             | V291H  |
|  | 5-0   | ●     | 45          |                   | 36             | V391H  |
|  | 5-0   | ○     | 70          |                   | 36             | V421H  |
|  | 4-0   | ○     | 45          |                   | 36             | V292ZH |
|  | 4-0   | ●     | 45          |                   | 12             | V392ZG |
|  | 3-0   | ○     | 45          |                   | 36             | V293H  |
|  | 3-0   | ●     | 45          |                   | 12             | V393G  |
|  | 3-0   | ●     | 45          |                   | 36             | V393H  |
|  | 3-0   | ○     | 70          |                   | 36             | V423H  |
|  | 3-0   | ●     | 70          |                   | 36             | V398H  |
|  FS-2S<br>19 mm | 4-0   | ○     | 45          | Slimmed           | 36             | V292H  |
|  | 4-0   | ●     | 45          | Slimmed           | 36             | V392H  |
|  | 4-0   | ○     | 70          | Slimmed           | 36             | V422H  |
|  | 4-0   | ●     | 70          | Slimmed           | 36             | V397H  |
|  FS-1<br>24 mm  | 4-0   | ○     | 70          |                   | 36             | V441H  |
|  | 4-0   | ●     | 70          |                   | 36             | V451H  |
|  | 3-0   | ○     | 70          |                   | 36             | V442H  |
|  | 3-0   | ●     | 70          |                   | 36             | V452H  |
|  | 2-0   | ○     | 70          |                   | 36             | V443H  |
|  | 2-0   | ●     | 70          |                   | 36             | V453H  |
|  FSL<br>30 mm | 3-0   | ○     | 70          |                   | 36             | V588H  |
|  | 3-0   | ●     | 70          |                   | 36             | V585H  |
|  | 2-0   | ○     | 75          |                   | 36             | JV589  |
|  | 2-0   | ●     | 70          |                   | 36             | V586H  |
|  | 0     | ○     | 70          |                   | 36             | V520H  |
|  | 0     | ●     | 70          |                   | 36             | V587H  |

| ▲ 3/8 Circle Conventional Cutting PRIME <sup>®</sup> Needles                                       |       |       |             |                        |                |          |
|--|-------|-------|-------------|------------------------|----------------|----------|
| Needle   | Gauge | Color | Length (cm) | Other information      | Number per box | Code     |
|  PC-3<br>16 mm  | 5-0   | ○     | 45          | MULTIPASS <sup>®</sup> | 36             | MPV9505H |
|  | 5-0   | ○     | 45          |                        | 24             | W9505T   |
|  | 4-0   | ○     | 45          | MULTIPASS <sup>®</sup> | 36             | MPV9506H |
|  PC-5<br>19 mm  | 3-0   | ○     | 70          | MULTIPASS <sup>®</sup> | 36             | MPV9571H |
|  PC-25<br>26 mm | 4-0   | ○     | 70          | MULTIPASS <sup>®</sup> | 36             | MPV9580H |
|  | 4-0   | ○     | 75          |                        | 24             | W9580T   |
|  | 3-0   | ○     | 70          | MULTIPASS <sup>®</sup> | 36             | MPV9581H |
|  | 3-0   | ○     | 75          |                        | 24             | W9581T   |

| ▲ Straight Cutting Needles   |       |       |             |                   |                |         |  |
|--|-------|-------|-------------|-------------------|----------------|---------|--|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code    |  |
|  SC-1<br>13 mm  | 4-0   | ●     | 45          |                   | 36             | V383H   |  |
|  KS-25<br>25 mm | 3-0   | ●     | 70          |                   | 12             | V2530G  |  |
|  TS<br>48 mm    | 3-0   | ○     | 70          |                   | 36             | AB2673H |  |
|  KS<br>60 mm    | 4-0   | ○     | 70          |                   | 36             | V662H   |  |
|  | 3-0   | ●     | 70          |                   | 36             | V523H   |  |
|  | 3-0   | ○     | 70          |                   | 36             | V663H   |  |
|  | 2-0   | ●     | 70          |                   | 36             | V524H   |  |
|  | 2-0   | ○     | 70          |                   | 36             | V664H   |  |




| ▼ 1/2 Circle MICROPOINT* Spatula  |       |       |             |                   |                |       |  |
|---|-------|-------|-------------|-------------------|----------------|-------|--|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code  |  |
|  GS-14 GS-14<br>5,5 mm | 10-0  | ●     | 30          |                   | 12             | V450G |  |
|   | 9-0   | ●     | 30          |                   | 12             | V449G |  |
|   | 8-0   | ●     | 20          |                   | 12             | V574G |  |
|  TG175-8<br>7 mm     | 7-0   | ●     | 45          |                   | 12             | W9565 |  |


| ▼ 3/8 Circle MICROPOINT* Spatula  |       |       |             |                   |                |       |  |
|---|-------|-------|-------------|-------------------|----------------|-------|--|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code  |  |
|  GS-9<br>6,5 mm      | 8-0   | ●     | 30          |                   | 12             | V120G |  |
|   | 7-0   | ●     | 30          |                   | 12             | V119G |  |
|  GS-9 GS-9<br>6,5 mm | 10-0  | ●     | 30          | Monofilament      | 12             | V440G |  |
|   | 9-0   | ●     | 30          |                   | 12             | V549G |  |
|   | 9-0   | ●     | 30          | Monofilament      | 12             | V439G |  |
|   | 8-0   | ●     | 20          |                   | 12             | V547G |  |
|   | 8-0   | ●     | 30          |                   | 12             | V548G |  |
|   | 7-0   | ●     | 45          |                   | 12             | V546G |  |


| ▼ 1/4 Circle MICROPOINT* Spatula  |       |       |             |                   |                |        |  |
|---|-------|-------|-------------|-------------------|----------------|--------|--|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code   |  |
|  TG100-8<br>6,5 mm | 6-0   | ●     | 45          |                   | 12             | JV7544 |  |


# VICRYL\*


(Polyglactin 910) Braided and Monofilament




| ▼ 3/8 Circle MICROPOINT* Reverse Cutting Needles                                      |       |       |             |                   |                |          |
|---|-------|-------|-------------|-------------------|----------------|----------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code     |
|  G-6 | 8 mm  | 6-0   | ●           | 45                |                | 12 V551G |
|  G-1 | 11 mm | 6-0   | ●           | 45                |                | 12 V554G |
|  G-3 | 13 mm | 5-0   | ●           | 45                |                | 12 V557G |


| ▼ 3/8 Circle CS ULTIMA* Spatula  |        |       |             |                   |                |          |
|--|--------|-------|-------------|-------------------|----------------|----------|
| Needle   | Gauge  | Color | Length (cm) | Other information | Number per box | Code     |
|  UCS-35 | 6,2 mm | 10-0  | ●           | 15                | MONOFILAMENT   | 12 V429G |

| ▼ 1/8 Circle CS ULTIMA* Spatula   |        |       |             |                   |                |          |
|---|--------|-------|-------------|-------------------|----------------|----------|
| Needle  | Gauge  | Color | Length (cm) | Other information | Number per box | Code     |
|  UCS-26 | 6,2 mm | 10-0  | ●           | 10                | MONOFILAMENT   | 12 V865G |

| ▼ 3/8 Circle Spatula Needles  |       |       |             |                   |                |          |
|---|-------|-------|-------------|-------------------|----------------|----------|
| Needle  | Gauge | Color | Length (cm) | Other information | Number per box | Code     |
|  SPAT-10 | 11 mm | 5-0   | ○           | 45                |                | 12 W9761 |

| ▼ 1/2 Circle Spatula Needles   |       |       |             |                   |                |          |
|--|-------|-------|-------------|-------------------|----------------|----------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code     |
|  S-22 | 8 mm  | 6-0   | ●           | 45                |                | 12 W9566 |
|  |       | 6-0   | ○           | 45                |                | 12 W9756 |

| ▼ 1/4 Circle Spatula Needles   |       |       |             |                   |                |          |
|--|-------|-------|-------------|-------------------|----------------|----------|
| Needle   | Gauge | Color | Length (cm) | Other information | Number per box | Code     |
|  S-4  | 8 mm  | 4-0   | ●           | 45                |                | 12 V572G |
|  S-29 | 8 mm  | 6-0   | ●           | 45                |                | 12 V555G |
|  S-14 | 8 mm  | 6-0   | ●           | 45                |                | 12 V570G |
|  |       | 6-0   | ●           | 45                | VISI-BLACK*    | 12 V575G |
|  |       | 6-0   | ○           | 45                |                | 12 V670G |
|  |       | 6-0   | ●           | 20                |                | 12 W9562 |
|  |       | 5-0   | ●           | 45                | VISI-BLACK*    | 12 V577G |
|  |       | 5-0   | ●           | 45                |                | 12 V571G |
|  |       | 5-0   | ○           | 45                |                | 12 V671G |

|  3/8 Circle Taper Point Needles |        |       |             |                   |                |      |       |
|--|--------|-------|-------------|-------------------|----------------|------|-------|
| Needle   | Gauge  | Color | Length (cm) | Other information | Number per box | Code |       |
| BV-6<br>                        | 4,8 mm | 10-0  | ●           | 10                | Monofilament   | 12   | V970G |
| BV-4<br>                        | 4,9 mm | 10-0  | ●           | 15                | Monofilament   | 12   | V971G |
| BV130-5<br>                     | 6,5 mm | 9-0   | ●           | 15                | Monofilament   | 12   | V239G |
|  |        | 8-0   | ●           | 20                |                | 12   | V400G |
| BV-1<br>                        | 9,3 mm | 6-0   | ●           | 45                |                | 12   | V301G |

| Ligatures |       |       |             |                   |                |        |  |
|-----------|-------|-------|-------------|-------------------|----------------|--------|--|
| Needle    | Gauge | Color | Length (cm) | Other information | Number per box | Code   |  |
| LIGAPAK*  | 4-0   | ●     | 250         | Reel              | 12             | V1204G |  |
|           | 3-0   | ●     | 250         | Reel              | 12             | V1205G |  |
|           | 2-0   | ●     | 250         | Reel              | 12             | V1206G |  |
|           | 0     | ●     | 250         | Reel              | 12             | V1207G |  |
|           | 1     | ●     | 250         | Reel              | 12             | V1208G |  |
|           | 4-0   | ●     | 125         | Reel              | 12             | V204G  |  |
|           | 3-0   | ●     | 125         | Reel              | 12             | V205G  |  |
|           | 2-0   | ●     | 125         | Reel              | 12             | V206G  |  |
|           | 0     | ●     | 125         | Reel              | 12             | V207G  |  |
| SUTUPAK*  | 3-0   | ●     | 140         |                   | 36             | V614H  |  |
|           | 2-0   | ●     | 140         |                   | 36             | V615H  |  |
|           | 0     | ●     | 140         |                   | 36             | V616H  |  |
|           | 1     | ●     | 140         |                   | 36             | V617H  |  |
|           | 2     | ●     | 140         |                   | 36             | V618H  |  |
| SUTUPAK*  | 4-0   | ●     | 2x70        |                   | 24             | V623E  |  |
|           | 4-0   | ○     | 2x70        |                   | 24             | V651E  |  |
|           | 3-0   | ●     | 2x70        |                   | 24             | V624E  |  |
|           | 3-0   | ○     | 2x70        |                   | 24             | V652E  |  |
|           | 2-0   | ●     | 2x70        |                   | 24             | V625E  |  |
|           | 2-0   | ○     | 2x70        |                   | 24             | V653E  |  |
|           | 0     | ●     | 2x70        |                   | 24             | V626E  |  |
|           | 0     | ○     | 2x70        |                   | 24             | V654E  |  |
|           | 1     | ●     | 2x70        |                   | 36             | V627H  |  |
|           | 2     | ●     | 2x70        |                   | 36             | V628H  |  |

**VICRYL\***  
(Polyglactin 910) Braided and Monofilament

| Ligatures |       |       |             |                   |                |        |
|-----------|-------|-------|-------------|-------------------|----------------|--------|
| Needle    | Gauge | Color | Length (cm) | Other information | Number per box | Code   |
| SUTUPAK*  | 5-0   | ●     | 3x45        |                   | 36             | V632H  |
|           | 5-0   | ○     | 3x45        |                   | 36             | V642H  |
|           | 4-0   | ●     | 3x45        |                   | 36             | V633H  |
|           | 4-0   | ○     | 3x45        |                   | 36             | V643H  |
|           | 3-0   | ●     | 3x45        |                   | 36             | V634H  |
|           | 3-0   | ○     | 3x45        |                   | 36             | V644H  |
|           | 2-0   | ●     | 3x45        |                   | 36             | V635H  |
|           | 2-0   | ○     | 3x45        |                   | 36             | V645H  |
|           | 0     | ●     | 3x45        |                   | 24             | V636E  |
|           | 1     | ●     | 3x45        |                   | 24             | V637E  |
|           | 1     | ○     | 3x45        |                   | 24             | V647E  |
|           | 2     | ●     | 3x45        |                   | 36             | V638H  |
| SUTUPAK*  | 4-0   | ●     | 5x70        |                   | 24             | V1214E |
|           | 3-0   | ●     | 5x70        |                   | 24             | V1215E |
|           | 2-0   | ●     | 5x70        |                   | 24             | V1216E |
|           | 0     | ●     | 5x70        |                   | 24             | V1217E |
|           | 0     | ○     | 5x70        |                   | 24             | V965E  |
|           | 1     | ●     | 5x70        |                   | 36             | V1218H |
|           | 2     | ●     | 5x70        |                   | 36             | V1219H |
| SUTUPAK*  | 5-0   | ●     | 6x45        |                   | 36             | V1223H |
|           | 4-0   | ●     | 6x45        |                   | 36             | V1224H |
|           | 3-0   | ●     | 6x45        |                   | 36             | V1225H |
|           | 3-0   | ○     | 6x45        |                   | 36             | V978H  |
|           | 2-0   | ●     | 6x45        |                   | 36             | V1226H |
|           | 0     | ●     | 6x45        |                   | 24             | V1227E |
|           | 1     | ●     | 6x45        |                   | 24             | V1228E |
|           | 2     | ●     | 6x45        |                   | 36             | V1229H |
| SUTUPAK*  | 4-0   | ●     | 12x45       |                   | 36             | V903H  |
|           | 3-0   | ●     | 12x45       |                   | 36             | V904H  |
|           | 3-0   | ○     | 12x45       |                   | 36             | V910H  |
|           | 2-0   | ●     | 12x45       |                   | 24             | V905E  |
|           | 2-0   | ○     | 12x45       |                   | 24             | V911E  |
|           | 0     | ●     | 12x45       |                   | 24             | V908E  |
|           | 0     | ○     | 12x45       |                   | 24             | V912E  |
|           | 1     | ●     | 12x45       |                   | 24             | V907E  |