

# ETHIBOND\* Excel

Polybutylate Coated Polyester

## SUTURE

### Description:

Braided  
Coated

For easy handling and secure knot tying.  
For smooth tie down and easy passage through tissue.

Synthetic  
Non-absorbable

For minimal tissue reaction.  
Provides permanent tensile strength retention in tissue.

### Color:

Green or white.

### Range:

7-0 to 6 (USP). Supplied as needled sutures or ligatures.  
With or without pledgets.

### Indications:











ETHIBOND\* sutures are intended for use in general soft tissue approximation and/or ligation, including use in cardiovascular, ophthalmic and neurosurgical procedures. Typical areas of use include:

- Heart valve fixation
- Ligament and tendon repair
- Retraction sutures

Full details in the Instruction for Use included in every package.











**1/2 Circle Taper Point Needles**




Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 RB-2	13 mm	5-0	75		36	6710H
 TF	13 mm	4-0	75		36	EH7417H
 TF	13 mm	4-0	45	Pledgets	36	EH7420H
 RB-1	17 mm	5-0	75		36	6870H
		4-0	75		36	6871H
		3-0	75		36	6872H
		2-0	75		36	6873H
 RB-1	17 mm	5-0	75		36	6550H
		4-0	75		36	E6551H
		3-0	90		36	6558H
		2-0	90		12	W6760
 SH-1	22 mm	4-0	75		36	EH7397H
		3-0	75		36	EH7398H
		2-0	75		36	EH7399H
 SH	26 mm	3-0	75		36	6832H
		2-0	75		36	6833H
		0	75		36	6834H
		1	75		36	EH7528H
 SH	26 mm	4-0	90		36	6521H
		3-0	90		36	6522H
		2-0	90		36	6523H
		2-0	90	6x3 mm pledgets	36	P6523H
		2-0	10x75		6	W10B82
		0	90		36	6524H
 MH	36 mm	2-0	75		36	EH7490H
		0	75		36	EH7491H
 MH	36 mm	2-0	90		36	B843H

**ETHIBOND\* Excel**  
Polybutylate Coated Polyester


**1/2 Circle Taper Point Needles (Heavier Wire Diameter)**

Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 UCL 13 mm	1	●	75		36	EH7497H
 MO-7 MO-7 22 mm	2	●	75		36	EH7845H
 CT-2 28 mm	2-0	●	75		36	6411H
	0	●	75		36	EB2316H
 MO-6 28 mm	2	●/○	4x75		24	4TB7177E
 CT-1 38 mm	0	●	75		36	6424H
	1	●	75		36	6425H
 CT-1 CT-1 38 mm	0	●	75		36	PLL6375H
 CTX 48 mm	1	●	75		36	PN6376H
 XLH 70 mm	1	●	75		12	X190G




**3/8 Circle Taper Point Needles**

Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 BV-1 9,3 mm	7-0	●	75		36	EH7427H
 C-1 13 mm	6-0	●	75		36	6889H
	5-0	●	75		36	6890H
 BB 17 mm	4-0	●	75		36	6881H





**Fish Hook Taper Point Needles**

Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 ASH-30 30 mm	1	●	75		12	EB4127G







**● Straight Taper Point Needles**



Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 ST-4 19 mm	4-0	●	35		36	EH7418H
 STAW 65 mm	0	●	75		24	BLL6375E
 STA 65 mm	3	●	75		12	EH7479G



**▼ 1/2 Circle TAPERCUT\* Needles**



Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 V-5 17 mm	5-0	●	75		36	6951H
	4-0	●	75		36	EH7384H
	3-0	●	75		36	6953H
	2-0	●	75		36	6954H
 V-5 17 mm	4-0	●	75		36	6935H
	4-0	●/○	4x75		12	MEH7719LG
	3-0	●	75		36	6936H
	3-0	●/○	4x75		12	6959G
	2-0	●	75		36	6937H
	2-0	●	75	6x3 mm pledgets	36	P6937H
	2-0	●	4x75		12	6937LG
	2-0	●/○	4x75		12	EH7712LG
	2-0	●/○	4x75	6x3 mm pledgets	12	EH7715LG
	2-0	●/○	4x75	3x3 mm soft pledgets	12	PX1011
	2-0	●	8x75	6x3 mm pledgets	6	MEH6937N
	2-0	●/○	8x75		6	MEH7712N
	2-0	●/○	8x75	6x3 mm pledgets	6	MEH7715N
	2-0	●/○	10x75	3x3 mm pledgets	6	W10B54
	2-0	○	90		12	W6917
	2-0	●	90	3x3 mm pledgets	36	D9813
2-0	○	90	3x3 mm pledgets	36	D9814	
 V-7 26 mm	3-0	●	75		36	6963H
	2-0	●	75		36	6964H
	0	●	75		36	6965H
 V-7 26 mm	3-0	●	75		36	6976H
	2-0	●	75		36	6977H
	2-0	○	75		36	6987H
	2-0	●	75	6x3 mm pledgets	36	P6977H
	2-0	●/○	4x75		12	EH7711LG
	2-0	●/○	4x75	6x3 mm pledgets	12	EH7716LG
	2-0	●/○	4x75	3x3 mm soft pledgets	12	PX1010
	2-0	●/○	8x75	6x3 mm pledgets	6	MEH7716N
	2-0	●/○	10x75	6x3 mm pledgets	6	W10B77
	0	●	90		36	6905H
	0	●/○	8x90	6x3 mm pledgets	6	MEH7717N








**ETHIBOND\* Excel**  
Polybutylate Coated Polyester









▼ 1/2 Circle TAPERCUT* Needles (Heavier Wire Diameter)							
Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code	
 V-34	38 mm	1	●	90		36	EB4407H
 V-37	40 mm	2	●	75		12	889G
 BPT-2	40 mm	6	●	75		12	RS72G
 V-39	45 mm	2	●	4x75		12	W4843
 BPT-1	48 mm	6	●	75		12	RS71G
 V-65	55 mm	5	●	75		12	BE3294
		5	●	4x75		12	W4846

▼ 3/8 Circle TAPERCUT* Needles							
Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code	
 V-4	17 mm	4-0	●	75		36	6942H
		3-0	●	75		36	6943H
		2-0	●	75		36	6944H
 V-4	17 mm	2-0	●	75		36	B927H
		2-0	●	90		36	HAA6395H
		2-0	●	90	6x3 mm pledgets	36	X32200

▼ Compound Curve TAPERCUT* Needles							
Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code	
 DA-1 <b>VISI-BLACK</b>	13 mm	4-0	●	45	VISI-BLACK*	12	18537G
 DA <b>VISI-BLACK</b>	25 mm	4-0	●	45	VISI-BLACK*	12	18538G




 <b>Straight TAPERCUT* Needles</b>							
Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code	
 VS-25	25 mm	4-0	45		12	W6584	


 <b>1/2 Circle Reverse Cutting Needles (Heavier Wire Diameter)</b>							
Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code	
 X-1	22 mm	3-0	75		36	EH7678H	
		2-0	75		36	EH7679H	
 OS-4	22 mm	0	75	HEAVY NEEDLE	36	6517H	
		1	75	HEAVY NEEDLE	36	6518H	
 OS-4	22 mm	2	90	HEAVY NEEDLE	12	W6748	
 CP-2	26 mm	0	75		36	EH7673H	
 CP-1	36 mm	0	75		36	X32049	
		1	75		36	EH7674H	
 CP	40 mm	0	75		36	EB2236H	


 <b>3/8 Circle Reverse Cutting Needles</b>							
Needle	Gauge	Suture Color	Length (cm)	Other information	Number per box	Code	
 FS-2	19 mm	5-0	45		36	6661H	
		3-0	45		36	EH7346H	
 FS-2S	19 mm	4-0	45	Slimmed	36	6683H	
 FS-1	24 mm	3-0	45		36	6663H	
 FS	26 mm	2-0	45		36	6664H	
 FSL	30 mm	0	75		36	EH7688H	
 FSLX	36 mm	0	75		36	EH7562H	
 LR	76 mm	5	50		12	B409TG	

# ETHIBOND\* Excel

Polybutylate Coated Polyester

▼ 3/8 Circle Reverse Cutting PRIME* Needles							
Needle		Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 P-1	11 mm	6-0	●	45		36	6697H
 P-3	13 mm	5-0	●	45		36	6698H
		4-0	●	45		36	EH7573H
		4-0	○	45		36	JA6442H
 PS-3	16 mm	5-0	●	45		36	6681H
		4-0	●	45		36	EH7760H

▲ Straight Cutting Needles							
Needle		Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 KS	60 mm	3-0	●	75		36	EH7722H
		1	●	75		36	X32030

▲ Ski Cutting Needles							
Needle		Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
 PB-1	22 mm	3-0	●	45		36	EH7579H

Ligatures							
		Gauge	Suture Color	Length (cm)	Other information	Number per box	Code
SUTUPAK*		3-0	●	2x70		36	EH6453H
		2-0	●	2x70		36	EH6454H
		0	●	2x70		36	EH6455H
		1	●	2x70		36	EH6456H
		2	●	2x70		36	EH6457H
		3	●	2x70		36	EH6458H
		5	●	2x70		36	EH6459H
SUTUPAK*		4-0	●	3x45		36	EH6432H
		3-0	●	3x45		36	EH6433H
		2-0	●	3x45		36	EH6434H
		0	●	3x45		36	EH6435H
		1	●	3x45		36	EH6436H
		2	●	3x45		36	EH6437H
SUTUPAK*		3-0	●	5x70		36	EH6523H
		2-0	●	5x70		36	EH6524H
		0	●	5x70		36	EH6525H
SUTUPAK*		5-0	●	6x45		36	EH6441H
SUTUPAK*		5-0	●	12x45		36	EH6371H
		4-0	●	12x45		36	EH6372H
		2-0	●	12x45		36	EH6374H
		0	●	12x45		24	EH6375E