


| | | | |
|-----------------------------|---|-----------------|----|
| Product Name | Superset double swivel catheter mount 22F-22M/15F, 70mm-150mm | | |
| Reference numbers | 3512000 | | |
| Product Type | Catheter Mount | | |
| Manufacturer | Intersurgical | | |
| Materials | HDPE | PP | SB |
| Packaging | | | |
| Unit Packaging | Individually packaged | | |
| Box quantity | 75 | | |
| Pallet quantity | 4800 | | |
| Instructions for Use | Instructions for use with product | | NO |
| | Instructions for use with each box | | NO |
| Certification | CE0120 | Class 2A | |
| Applicable Standards | BS EN ISO 13485: Medical devices — Quality management systems — Requirements for regulatory purposes | | |
| | ISO 9001: Quality Management Systems - Requirements | | |
| | ISO 15223-1: Medical Devices - Symbols to be Used with Medical Device Labels, Labelling, & Information to be Supplied | | |
| | BS EN ISO 5356-1: Anaesthetic and respiratory equipment Conical connectors. Cones and sockets. | | |
| | BS 7143: Catheter mounts (flexible adaptors) for use with medical breathing systems | | |
| Sterile | No | | |
| Shelf life | 5 Years | | |
| Disposal Methods | As hospital guidelines | | |
| Re-use |  | Single use only | |

Product characteristics

Technical information

| | EXTENDED | COMPACT |
|---------------------------------------|---------------|---------|
| Length (mm) | 150 | 70 |
| Resistance to flow at 30 L/min (mbar) | 0.3 | 0.3 |
| Compressible volume (ml) | 47.5 | 26.6 |
| Weight (g) | 18.1 | |
| Leakage at 60 mbar (ml/min) | 1.6 | |
| Connectors (Machine / Patient) | 22F / 22M/15F | |



**Material
Abbreviations**

| | |
|------|---------------------------------|
| ABS | Acrylonitrile Butadiene Styrene |
| AL | Aluminium |
| HDPE | High Density Polyethylene |
| HIPS | High Impact Polystyrene |
| LDPE | Low Density Polyethylene |
| MBS | Methacrylate Butadiene Styrene |
| NRL | Natural Rubber Latex |
| PC | Polycarbonate |
| PE | Polyethylene |
| PP | Polypropylene |
| PVC | Poly Vinyl Chloride |
| SB | Styrene Butadiene |
| Si | Silicone |
| SS | Stainless Steel |
| TPE | Thermoplastic Elastomer |
| SBC | Styrene Butadiene Copolymer |

