

VICRYL*
(Polyglactin 910) Braided and Monofilament

SUTURE

Description:	Braided	For easy handling and secure knot tying.
	Coated	For smooth passage through tissue and easy knot tie down.
	Synthetic	For minimal tissue reaction.
	Absorbable	By hydrolysis. Essentially complete in 56-70 days.

Tensile strength:	Post implantation	Approximate % original strength remaining
	14 days	75%
	21 days	50% (6-0 and larger) 40% (7-0 and smaller)
	28 days	25% (6-0 and larger)

Color: Violet or undyed.












Range: 10-0 to 2 (USP). Supplied as needed sutures and ligatures. Sizes 10-0 and 9-0 are monofilament in structure.

Indications: VICRYL* sutures are intended for use in soft tissue approximation and/or ligation, including use in ophthalmic surgery, peripheral nerve adaptation and microsurgery for vessels less than 2 mm in diameter. Typical areas of use include:







- Fascia closure - due to the unique 28-day claim
- Subcutaneous fat
- Joint capsule
- Uterus








Full details in the Instruction for Use included in every package.








1/2 Circle Taper Point Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 TF-6 6,5 mm	8-0	●	30		12	V1027G	
	7-0	●	30		36	V1028H	
 TF-1 10 mm	5-0	●	70		36	V133H	
 RB-2 13 mm	6-0	●	70		36	PZ2571H	
 TF 13 mm	6-0	●	70		36	V926H	
	5-0	●	70		36	V925H	
	4-0	●	70		36	V924H	
 RB-1 17 mm	6-0	●	70		36	V302H	
	5-0	●	70		36	V303H	
	5-0	○	70		36	V213H	
	4-0	●	70		36	V304H	
	4-0	○	70		36	V214H	
	4-0	●	8x45	CONTROL RELEASE*	24	V734E	
	4-0	●	4x45	CONTROL RELEASE*	12	V735G	
	4-0	●	8x70	CONTROL RELEASE*	24	V799E	
	3-0	●	70		36	V305H	
	3-0	○	70		36	V215H	
	3-0	●	8x45	CONTROL RELEASE*	12	J713D	
2-0	●	70		36	V306H		
 RB-1 RB-1 17 mm	3-0	●	70		36	V667H	
 JRB-1  VISI-BLACK 17 mm	5-0	●	70	VISI-BLACK*	36	V3030H	
	4-0	●	70	VISI-BLACK*	36	V3040H	
 SH-1 22 mm	4-0	●	70		36	V310H	
	4-0	○	70		36	V426H	
	3-0	●	70		36	V311H	
	3-0	○	70		36	V219H	
	3-0	●	4x45	CONTROL RELEASE*	36	V782H	
	2-0	●	70		36	V312H	
	2-0	○	70		36	V220H	
	2-0	●	8x45	CONTROL RELEASE*	24	V792E	
 JB-1  VISI-BLACK 22 mm	4-0	●	70	VISI-BLACK*	36	V3100H	
	3-0	●	70	VISI-BLACK*	36	V3110H	
	2-0	●	70	VISI-BLACK*	36	V3120H	





VICRYL*
(Polyglactin 910) Braided and Monofilament


 1/2 Circle Taper Point Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 SH 26 mm	4-0	●	70		36	V315H
	4-0	●	8x70	CONTROL RELEASE*	12	V783G
	3-0	●	70		36	V316H
	3-0	○	70		36	V416H
	3-0	●	90		36	V242H
	3-0	●	4x45	CONTROL RELEASE*	36	V780H
	3-0	●	8x45	CONTROL RELEASE*	12	J774D
	3-0	●	8x70	CONTROL RELEASE*	12	J784D
	2-0	●	70		36	V317H
	2-0	○	70		36	V224H
	2-0	●	90		36	V243H
	2-0	●	8x45	CONTROL RELEASE*	12	J775D
	0	●	70		36	V318H
	0	○	70		36	V225H
 JB VISI-BLACK 26 mm	4-0	●	70	VISI-BLACK*	36	V3150H
	3-0	●	70	VISI-BLACK*	36	V3160H
	3-0	○	70	VISI-BLACK*	36	V4416H
	2-0	●	70	VISI-BLACK*	36	V3170H
 MH-1 31 mm	3-0	●	70		36	V245H
	2-0	●	70		36	V246H
	0	●	70		36	V247H
 MH 36 mm	4-0	●	90		36	PG2592H
	3-0	●	70		36	V322H
	3-0	●	90		36	V100H
	2-0	●	70		36	V323H
	2-0	○	70		36	V226H
	2-0	●	90		36	V101H
	0	●	70		36	V324H
	0	●	90		36	V102H
	1	●	70		36	V325H
	1	○	70		36	V228H
 LH 40 mm	2-0	●	70		36	PH2574H





 1/2 Circle Taper Point Needles (Heavier Wire Diameter)						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 UCL 13 mm	3-0	●	70		36	V113H
	0	●	70		36	V115H
 UCLX 16 mm	3-0	●	70		36	V13H
	2-0	●	70		36	V14H
	0	●	70		36	V15H
	1	●	70		36	V16H
 CT-3 22 mm	3-0	●	70		36	V327H
	2-0	●	70		36	V328H
	0	●	70		36	V329H
 CT-2 26 mm	3-0	●	70		36	V332H
	2-0	●	70		36	V333H
	2-0	○	70		36	V289H
	2-0	●	4x45	CONTROL RELEASE*	24	V7842E
	0	●	70		36	V334H
	0	○	70		36	V270H
	0	●	8x45	CONTROL RELEASE*	24	V744E
	0	●	4x70	CONTROL RELEASE*	24	4PK2575YE
	1	●	70		36	V335H
	2	●	70		36	V336H
 CT-1 36 mm	3-0	●	70		36	V338H
	3-0	○	90		36	V944H
	2-0	●	70		36	V339H
	2-0	●	90		36	V345H
	2-0	○	90		36	V945H
	2-0	○	8x70	CONTROL RELEASE*	12	J742D
	0	●	70		36	V340H
	0	●	90		36	V346H
	0	○	90		36	V946H
	0	●	8x45	CONTROL RELEASE*	12	J740D
	1	●	70		36	V341H
	1	●	90		36	V347H
	1	●	4x70	CONTROL RELEASE*	12	V736G
	2	●	90		36	V348H
2	○	90		36	V948H	
 MO-4 36 mm	0	●	70		36	V436H
	1	●	90		36	V255H





VICRYL*
(Polyglactin 910) Braided and Monofilament



 1/2 Circle Taper Point Needles (Heavier Wire Diameter)						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 CT 40 mm	3-0	●	70		36	V350H
	2-0	●	70		36	V351H
	2-0	●	8x45	CONTROL RELEASE*	12	8PM2544YG
	0	●	70		36	V352H
	0	●	90		36	V358H
	0	●	150	LOOP	24	V1407E
	1	●	70		36	V353H
	1	●	90		36	V359H
	1	●	8x45	CONTROL RELEASE*	12	J753D
	2	●	90		36	V360H
	2	○	90		36	V960H
	 CTX 48 mm	3-0	●	70		36
2-0		●	70		36	V363H
0		●	70		36	V364H
0		●	90		36	V370H
0		○	90		36	V170H
0		●	8x45	CONTROL RELEASE*	12	J764D
1		●	70		36	V365H
1		●	90		36	V371H
1		○	90		36	V366H
1		●	8x45	CONTROL RELEASE*	12	J765D
2		●	90		36	V372H
2		○	90		36	V367H
 TP-1 65 mm		2	●	4x70		6
 XLH 70 mm	2-0	●	70		12	V581G
	0	●	70		12	V582G
	1	●	70		12	V583G


1/2 Circle ETHIGUARD® Blunt Point Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 MHB-1 31 mm	3-0	●	75		12	W9983
	2-0	●	75		12	W9984
 CTB-1 36 mm	2-0	●	75		12	W9985
	2-0	●	75	Heavy Needle	12	W9993
	0	●	75		12	W9986
	0	●	90	Heavy Needle	12	W9994
	1	●	90	Heavy Needle	12	W9995
 CTB 40 mm	0	●	75		12	W9988
	0	●	90	Heavy Needle	12	W9996
	1	●	90	Heavy Needle	12	W9997
 CTXB 48 mm	0	●	90		12	W9990
	1	●	90		12	W9991


3/8 Circle Blunt Point Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 BP-5 65 mm	1	●	100		12	W9391

5/8 Circle Taper Point Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 UR-6 26 mm	3-0	●	70		36	V601H
	2-0	●	70		36	V602H
	0	●	70		36	V603H
	1	●	70		36	VC2575H
 UR-6 26 mm	2-0	●	70		36	VCC2573H
 UR-5 36 mm	2-0	●	70		36	V375H
	0	●	70		36	V376H
	1	●	70		36	V377H
 UR-4 40 mm	2-0	●	70		36	V380H
	0	●	70		36	V381H

▼ 1/2 Circle TAPERCUT* Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 V-37	40 mm	2-0	●	90		36	VS4020H
		0	●	90		36	VS4000H
 V-37	40 mm	1	●	70		36	ODD2574H
 V-40	48 mm	2-0	●	90		36	VS5020H
		0	●	70		36	VS5000H
		1	●	150	LOOP	24	V829E
 BPT-1	48 mm	6	●	75		12	V140G
		6	●	150		12	OH2528G



▼ 3/8 Circle TAPERCUT* Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 V-18	13 mm	6-0	●	70		36	V991H
		5-0	●	70		36	V990H
 V-4	17 mm	4-0	○	70		12	V240G
		4-0	○	70		36	V240H




▼ 5/8 Circle TAPERCUT* Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 UW-10	10 mm	6-0	●	30		12	W9172




▼ Compound Curve TAPERCUT* Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 DA VISI-BLACK	25 mm	4-0	●	45	VISI-BLACK*	12	18531G

VICRYL*







(Polyglactin 910) Braided and Monofilament


● Fish Hook Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 PB-30 30 mm	2-0	●	70	Taper point	36	DF2570H
	1	●	70	Taper point	36	DF2573H
 V-38 31 mm	1	●	75	TAPERCUT*	12	W9335









● Straight Taper Point Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 ST-4 19 mm	4-0	●	70		36	BA2573H
	3-0	●	70		36	BA2574H
 ST-4 ST-4 19 mm	4-0	●	35		36	V620H
 ST 48 mm	3-0	●	70		36	BC2573H



▼ 1/2 Circle TAPERCUT* Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 V-5 17 mm	4-0	●	70		12	V994G
	4-0	●	70		36	V994H
	4-0	○	70		36	V230H
	3-0	●	70		36	V276H
 V-7 26 mm	3-0	●	70		12	V998G
	3-0	●	70		36	V998H
	2-0	●	70		36	V999H
	2-0	●	6x45	CONTROL RELEASE*	24	6OB2545YE
	0	●	70		36	V279H
 V-34 36 mm	3-0	●	90		36	V516H
	2-0	●	90		36	V517H
	0	●	90		36	V518H
	1	●	90		36	V519H
	1	○	90		36	V919H

VICRYL*
(Polyglactin 910) Braided and Monofilament





▼ 1/2 Circle Reverse Cutting Needles (Heavier Wire Diameter)							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 X-1	22 mm	3-0	●	70		36	V460H
		3-0	○	70		36	ME2673H
		2-0	●	70		36	V461H
		2-0	○	75		36	JV459
 OS-4	22 mm	0	○	70	HEAVY NEEDLE	36	V694H
		2	●	75	HEAVY NEEDLE	12	W9287
 CP-2	26 mm	3-0	●	70		36	MF2572H
		2-0	○	70		36	V869H
		0	●	70		36	MF2574H
		0	●	4x45	CONTROL RELEASE	24	V870E
		1	○	70		36	MF2675H
 CP-1	36 mm	3-0	●	70		36	V465H
		2-0	●	70		36	V466H
		2-0	●	90		36	V472H
		2-0	○	90		36	JV1472
		0	●	70		36	V467H
		0	●	90		36	V473H
		0	●	4x45	CONTROL RELEASE	12	V475G
		1	●	70		36	V468H
		1	●	90		36	V474H
		2	●	90		36	V482H
 CP	40 mm	2-0	●	70		36	V478H
		0	●	70		36	V479H
		0	●	90		36	V485H
		1	●	70		36	V480H
		1	●	90		36	V486H
 CPX	48 mm	0	●	90		36	V1057H
		1	●	90		36	V1058H
		2	●	90		36	V1059H




▼ 1/2 Circle Reverse Cutting PRIME* Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 PS-4	16 mm	5-0	○	45	Compound curve	12	W9436
		4-0	○	45	MULTIPASS*	36	MPV507H
		4-0	○	45		12	V507G
		4-0	○	45	Compound curve	12	W9437





▼ 3/8 Circle Reverse Cutting PRIME* Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 P-1	11 mm	6-0	○	45	MULTIPASS*	36	MPV489H
		6-0	○	45		36	V489H
		5-0	○	45	MULTIPASS*	36	MPV490H
		5-0	○	45		36	V490H
 P-3	13 mm	6-0	○	45	MULTIPASS*	36	MPV492H
		6-0	○	45		36	V492H
		5-0	○	45	MULTIPASS*	36	MPV493H
		5-0	○	45		36	V493H
		4-0	○	45	MULTIPASS*	36	MPV494H
		4-0	○	45		36	V494H
 PS-3	16 mm	5-0	○	45	MULTIPASS*	36	MPV500H
		4-0	○	45		24	W9508T
 PS-2	19 mm	5-0	○	45	MULTIPASS*	36	MPV495H
		4-0	○	45	MULTIPASS*	36	MPV496H
		4-0	○	45		24	W9515T
		3-0	○	45	MULTIPASS*	36	MPV497H
		3-0	○	45		36	V497H
 PS-2 S	19 mm	4-0	○	45	Slimmed	36	V496H
 PS-1	24 mm	3-0	○	45	MULTIPASS*	36	MPV683H
		3-0	○	45		36	V683H
		2-0	○	45	MULTIPASS*	36	MPV684H
		2-0	○	45		36	V684H
 PS	26 mm	3-0	○	70	MULTIPASS*	36	MPV9526H
 PSL	30 mm	2-0	●	70		36	V686H



▼ 3/8 Circle Reverse Cutting Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 C-3	13 mm	6-0	●	45		36	V384H
		5-0	●	45		36	V385H
		4-0	●	45		36	V386H
 FS-3	16 mm	6-0	●	45		36	V387H
		5-0	●	45		36	V388H



VICRYL*
(Polyglactin 910) Braided and Monofilament


▼ 3/8 Circle Reverse Cutting Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 FS-2 19 mm	5-0	○	45		36	V291H
	5-0	●	45		36	V391H
	5-0	○	70		36	V421H
	4-0	○	45		36	V292ZH
	4-0	●	45		12	V392ZG
	3-0	○	45		36	V293H
	3-0	●	45		12	V393G
	3-0	●	45		36	V393H
	3-0	○	70		36	V423H
	3-0	●	70		36	V398H
 FS-2S 19 mm	4-0	○	45	Slimmed	36	V292H
	4-0	●	45	Slimmed	36	V392H
	4-0	○	70	Slimmed	36	V422H
	4-0	●	70	Slimmed	36	V397H
 FS-1 24 mm	4-0	○	70		36	V441H
	4-0	●	70		36	V451H
	3-0	○	70		36	V442H
	3-0	●	70		36	V452H
	2-0	○	70		36	V443H
	2-0	●	70		36	V453H
 FSL 30 mm	3-0	○	70		36	V588H
	3-0	●	70		36	V585H
	2-0	○	75		36	JV589
	2-0	●	70		36	V586H
	0	○	70		36	V520H
	0	●	70		36	V587H

▲ 3/8 Circle Conventional Cutting PRIME [®] Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 PC-3 16 mm	5-0	○	45	MULTIPASS [®]	36	MPV9505H
	5-0	○	45		24	W9505T
	4-0	○	45	MULTIPASS [®]	36	MPV9506H
 PC-5 19 mm	3-0	○	70	MULTIPASS [®]	36	MPV9571H
 PC-25 26 mm	4-0	○	70	MULTIPASS [®]	36	MPV9580H
	4-0	○	75		24	W9580T
	3-0	○	70	MULTIPASS [®]	36	MPV9581H
	3-0	○	75		24	W9581T

▲ Straight Cutting Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 SC-1 13 mm	4-0	●	45		36	V383H	
 KS-25 25 mm	3-0	●	70		12	V2530G	
 TS 48 mm	3-0	○	70		36	AB2673H	
 KS 60 mm	4-0	○	70		36	V662H	
	3-0	●	70		36	V523H	
	3-0	○	70		36	V663H	
	2-0	●	70		36	V524H	
	2-0	○	70		36	V664H	




▼ 1/2 Circle MICROPOINT* Spatula							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 GS-14 GS-14 5,5 mm	10-0	●	30		12	V450G	
	9-0	●	30		12	V449G	
	8-0	●	20		12	V574G	
 TG175-8 7 mm	7-0	●	45		12	W9565	


▼ 3/8 Circle MICROPOINT* Spatula							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 GS-9 6,5 mm	8-0	●	30		12	V120G	
	7-0	●	30		12	V119G	
 GS-9 GS-9 6,5 mm	10-0	●	30	Monofilament	12	V440G	
	9-0	●	30		12	V549G	
	9-0	●	30	Monofilament	12	V439G	
	8-0	●	20		12	V547G	
	8-0	●	30		12	V548G	
	7-0	●	45		12	V546G	


▼ 1/4 Circle MICROPOINT* Spatula							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
 TG100-8 6,5 mm	6-0	●	45		12	JV7544	


VICRYL*


(Polyglactin 910) Braided and Monofilament




▼ 3/8 Circle MICROPOINT* Reverse Cutting Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 G-6	8 mm	6-0	●	45		12 V551G
 G-1	11 mm	6-0	●	45		12 V554G
 G-3	13 mm	5-0	●	45		12 V557G






▼ 3/8 Circle CS ULTIMA* Spatula						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 UCS-35	6,2 mm	10-0	●	15	MONOFILAMENT	12 V429G

▼ 1/8 Circle CS ULTIMA* Spatula						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 UCS-26	6,2 mm	10-0	●	10	MONOFILAMENT	12 V865G

▼ 3/8 Circle Spatula Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 SPAT-10	11 mm	5-0	○	45		12 W9761

▼ 1/2 Circle Spatula Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 S-22	8 mm	6-0	●	45		12 W9566
		6-0	○	45		12 W9756

▼ 1/4 Circle Spatula Needles						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
 S-4	8 mm	4-0	●	45		12 V572G
 S-29	8 mm	6-0	●	45		12 V555G
 S-14	8 mm	6-0	●	45		12 V570G
		6-0	●	45	VISI-BLACK*	12 V575G
		6-0	○	45		12 V670G
		6-0	●	20		12 W9562
		5-0	●	45	VISI-BLACK*	12 V577G
		5-0	●	45		12 V571G
		5-0	○	45		12 V671G

 3/8 Circle Taper Point Needles							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
BV-6 	4,8 mm	10-0	●	10	Monofilament	12	V970G
BV-4 	4,9 mm	10-0	●	15	Monofilament	12	V971G
BV130-5 	6,5 mm	9-0	●	15	Monofilament	12	V239G
		8-0	●	20		12	V400G
BV-1 	9,3 mm	6-0	●	45		12	V301G

Ligatures							
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code	
LIGAPAK*	4-0	●	250	Reel	12	V1204G	
	3-0	●	250	Reel	12	V1205G	
	2-0	●	250	Reel	12	V1206G	
	0	●	250	Reel	12	V1207G	
	1	●	250	Reel	12	V1208G	
	4-0	●	125	Reel	12	V204G	
	3-0	●	125	Reel	12	V205G	
	2-0	●	125	Reel	12	V206G	
	0	●	125	Reel	12	V207G	
SUTUPAK*	3-0	●	140		36	V614H	
	2-0	●	140		36	V615H	
	0	●	140		36	V616H	
	1	●	140		36	V617H	
	2	●	140		36	V618H	
SUTUPAK*	4-0	●	2x70		24	V623E	
	4-0	○	2x70		24	V651E	
	3-0	●	2x70		24	V624E	
	3-0	○	2x70		24	V652E	
	2-0	●	2x70		24	V625E	
	2-0	○	2x70		24	V653E	
	0	●	2x70		24	V626E	
	0	○	2x70		24	V654E	
	1	●	2x70		36	V627H	
	2	●	2x70		36	V628H	

VICRYL*
(Polyglactin 910) Braided and Monofilament

Ligatures						
Needle	Gauge	Color	Length (cm)	Other information	Number per box	Code
SUTUPAK*	5-0	●	3x45		36	V632H
	5-0	○	3x45		36	V642H
	4-0	●	3x45		36	V633H
	4-0	○	3x45		36	V643H
	3-0	●	3x45		36	V634H
	3-0	○	3x45		36	V644H
	2-0	●	3x45		36	V635H
	2-0	○	3x45		36	V645H
	0	●	3x45		24	V636E
	1	●	3x45		24	V637E
	1	○	3x45		24	V647E
	2	●	3x45		36	V638H
SUTUPAK*	4-0	●	5x70		24	V1214E
	3-0	●	5x70		24	V1215E
	2-0	●	5x70		24	V1216E
	0	●	5x70		24	V1217E
	0	○	5x70		24	V965E
	1	●	5x70		36	V1218H
	2	●	5x70		36	V1219H
SUTUPAK*	5-0	●	6x45		36	V1223H
	4-0	●	6x45		36	V1224H
	3-0	●	6x45		36	V1225H
	3-0	○	6x45		36	V978H
	2-0	●	6x45		36	V1226H
	0	●	6x45		24	V1227E
	1	●	6x45		24	V1228E
	2	●	6x45		36	V1229H
SUTUPAK*	4-0	●	12x45		36	V903H
	3-0	●	12x45		36	V904H
	3-0	○	12x45		36	V910H
	2-0	●	12x45		24	V905E
	2-0	○	12x45		24	V911E
	0	●	12x45		24	V908E
	0	○	12x45		24	V912E
	1	●	12x45		24	V907E